Model 8810



Synchro/Resolver Angle Position Indicator

- 0.001° Resolution
- 0.004° Accuracy
- 0-360° Display
- Auto Line-to-Line Select
- Up to 10 kHz Frequency Range
- $\pi/6$ Phase Sensitive Detection
- Auto Phase Correction
- Optional IEEE-488 for Remote Programmability



GENERAL DESCRIPTION

Based on North Atlantic Instruments Trig-Logic processor the Model 8810 truly represents a major step forward in Synchro/Resolver to digital converter technology. With a resolution of 0.001° this full tracking type II servo converter can track without velocity error to 200°/sec.

The Model 8810 has front panel controls and input terminations while retaining the rear I/O and programming of the model 8800.

 $\pi/6$ phase sensitive detection inherently rejects unwanted harmonics and noise contained in the incoming signal. Built-in auto-phase correction further reduces the possibility of errors caused by quadrature and harmonics when reference and signal are out of phase by as much as 30° .

The 8810 accepts any standard line-to-line level without pre selecting or programming the input signal. This unique feature is due to an autoranging circuit that displays the applied input signal voltage level on the front panel.

Two pushbutton front-panel selectable input channels are provided.

In the remote mode, the user can program the desired input channel. BCD outputs, data freeze and converter busy signals are standard features making the unit ideal for ATE applications requiring "hands-off operation".

A bright, easy to read, 0.55" Plasma Display makes the unit an easy to read instrument even in bright light.

Options include low band frequency response (47 to 440 Hz).

SPECIFICATIONS

 $\textbf{Resolution}..... 0.001^{\circ}$

Input Channels...... 2

11.8, 26, or 90 V_{L-L} auto-ranging

Ch.2: Resolver

11.8, 26, or 90 $V_{L\text{-}L}$ auto-ranging

(Non-standard input levels available; consult factory)

Accuracy..... $\pm 0.004^{\circ}$ (standard)

Frequency Range....... 360-1200 Hz (standard) or 47-440 Hz (optional)

360-10kHz (consult factory)

Angular Range...... 0.000°-359.999° (*standard*)

Reference Voltage...... 3 V to 115 V (AGC)

Reference: $100 \text{ k}\Omega \text{ min.}$

Tracking Speed...... 200°/s (standard)

75°/s (with 47-440 Hz option)

Settling Time..... 1.5 s max. for 180° step change

3.0 s max (with 47-440 Hz option)

Digital Output...... 6 decade BCD (1-2-4-8) 10 TTL loads

Logic 1: +2.5 V min Logic 0: +0.6 V max

Data Availability...... Continuous or data freeze; DF (J1 pin 42)

Track = 0 V or open; freeze = +5 V; DF (J1 pin 27)

Track = +5 V or open; freeze = 0 V

Auto Phase Correction.... Unit automatically corrects for up to a ±30° phase shift between stator and rotor signals

Converter Busy...... TTL compatible pulses, 1µs wide (nom.) Pulses present when tracking

Temperature Range...... 0-70°C (operating) standard

47-440 Hz; 25 VA max.


Mating Connector...... Included with 8810 (Refer to page 7 for details)

Weight..... 8 lbs.

CONTROLS AND INDICATORS

| Control or Indicator | Function | | |
|--|---|--|--|
| OFF push button | Turns power off. | | |
| SYN push button | When pressed in, selects Synchro operation and turns power on. If optional IEEE-488 interface is installed, and API is in Remote mode (see Remote push button below), the interface may select either Synchro or Resolver operation. | | |
| SYN LED | Optional LED used on units with IEEE-488 or MATE/CIIL interfaces. When lit, indicates Synchro operation has been selected. | | |
| RES push button | When pressed in, selects Resolver operation and turns power on. If optional IEEE-488 interface is installed, and API is in Remote mode (see Remote push button below), the interface may select either Synchro or Resolver operation. | | |
| RES LED | Optional LED used on units with IEEE-488 interface. When lit, indicates Resolver operation has been selected. | | |
| REM push button | When pressed in, allows remote programming of Synchro or Resolver operation via rear panel remote connector and turns power on. | | |
| | When pressed in, and if optional IEEE-488 interface is installed, allows remote control of Synchro or Resolver operation via interface. If the IEEE-488 local lockout bus command is received by the API, remote control of Synchro or Resolver operation via the interface is allowed if either the SYN, RES, or REM push button is pressed in. | | |
| REM LED | Optional LED used on units with IEEE-488 or MATE/CIIL interfaces. When lit, indicates that the API is in Remote mode. | | |
| Numeric display | Displays angular information in degrees and decimal degrees. | | |
| HOLD momentary push button | Freezes display when pushed in. | | |
| 115 V - 230 V Power switch (located on main chassis) | Allows unit to operate from either 115 V or 230 V power source | | |
| EXT-INT Reference switch (located on main chassis) | Provides a means of switching reference as required in calibration procedure. Normally is set to INT. | | |
| 90 V LED | When lit, indicates that input signal is 90 V L-L. | | |
| 26 V LED | When lit, indicates that input signal is 26 V L-L. | | |
| 11.8V LED | When lit, indicates that input signal is 11.8 V L-L. | | |
| S1, S2, S3 or S4 terminals | Accepts Synchro or Resolver input data. | | |
| HI, LO REF terminals | Accepts input reference voltage. | | |
| GND terminal | Chassis ground | | |
| Power switch (rear panel) | Transfers power input to rear panel connector, J1 for use in rack mounted units | | |

MECHANICAL OUTLINE DRAWING



North Atlantic Industries, Inc. 110 Wilbur Place, Bohemia, NY 11716 631.567.1100 / 631.567.1823 (fax) www.naii.com / e-mail:sales@naii.com 2-13-02 Cage Code: OVGU1 8810A001 Rev. C Page 4 of 7

PROGRAMMING SPECIFICATIONS

Line-to-LineThe 8810 senses line-to-line level automatically and indicates the level selected on the front panel mounted LED's.

Mode The 8810 has Channel 1 pre-selected for Synchro inputs and Channel 2 for Resolver inputs.

Channel 1 Channel 2

Resolver: Pin 34 open Resolver: Pin 18 open

Synchro: jumper pin 34 and 35 Synchro: jumper pin 18 and 35

Channel Selection The front panel buttons allow the selection Synchro or Resolver on the 8810. Channel selection may also be done remotely by

depressing the REM button and programming J1 as follows:

Channel 1: Pin 43 0 V or ground Channel 2: Pin 43 +5 V or open

A +5 V output on pin 20 indicates that the Angle Position Indicator is set for local operation; 0 V output indicates it is in the remote mode.

IEEE Interface: When the IEEE NATIVE interface option is ordered, rear panel ground connections, tilt stand, and mounting feet are deleted. Power, reference, and signal inputs are applied through standard 50-pin input connector J5. It does not contain the following logic signals: BCD outputs, data freeze, and converter busy.

The logic signals are connected to the IEEE board which interfaces with the external computer lines by way of IEEE standard 24-pin connector J6 (Table 2-3).

If desired, the unit may be operated as a standard API with BCD outputs and data freeze by removing P1 from J1 and connecting the input connector to J1 (power must then be applied to appropriate pins of J5). This mode of operation is convenient for servicing and alignment of the main API board.

J5 Pin Designation (IEEE)

Function

S1(X)

R2

Do Not Use

Spare Spare

Do Not Use

Power Input High Power Input Low Case Ground Digital Ground

6 S2 (Z) Synchro 7 S3 (Y) 8 Spare 9 **R**1 Synchro Reference 10 R2 11-18 Do Not Use 19 Spare 20 Spare 21 **S**1 22 S2 Resolver 23 S3 24 **S4** 25 **R**1 Resolver Reference

J6 Pin Designations (IEEE)

| Pin | Designations |
|-----|--------------|
| 1 | D101 |
| 2 | D102 |
| 3 | D103 |
| 4 | D104 |
| 5 | EOI |
| 6 | DAV |
| 7 | NRFD |
| 8 | NDAC |
| 9 | IFC |
| 10 | SRQ |
| 11 | ATN |
| 12 | Shield |
| 13 | D105 |
| 14 | D106 |
| 15 | D107 |
| 16 | D108 |
| 17 | REN |
| 18 | Gnd, DAV |
| 19 | Gnd, NRFD |
| 20 | Gnd, NDAC |
| 21 | Gnd, IFC |
| 22 | Gnd, SRQ |
| 23 | Gnd, ATN |
| 24 | Gnd, Logic |
| | |

North Atlantic Industries, Inc. 110 Wilbur Place, Bohemia, NY 11716

Pin

1

2

3

4 5

26 27-35

36

37 38-50

> 631.567.1100 / 631.567.1823 (fax) www.naii.com / e-mail:sales@naii.com

2-13-02

Cage Code: OVGU1


8810A001 Rev. C Page 5 of 7

J1 Pin Designations

| Pin | Function | | |
|-----|------------------|------|--------------------|
| 1 | Power Input High | | |
| 2 | Power Input Low | | |
| 3 | Case ground | | |
| 4 | Digital ground | _ | |
| 5 | S1 (X) | | |
| 6 | S2 (Z) | | Synchro |
| 7 | S3 (Y) | | |
| 8 | Not used | _ | |
| 9 | R1 | | Synchro Reference |
| 10 | R2 | | |
| 11 | Converter busy | | |
| 12 | 0 . 04° | | |
| 13 | 0 . 01° | | |
| 14 | 0 . 8° | | BCD Outputs |
| 15 | 0 . 2° | | |
| 16 | 4° | | |
| 17 | 1° | | |
| 18 | Not used | | |
| 19 | Spare Spare | | |
| 20 | REM | | |
| 21 | S1 | | |
| 22 | S2 | | Resolver |
| 23 | S3 | | _ |
| 24 | S4 | | |
| 25 | R1 | | Resolver Reference |
| 26 | R2 | | = |
| 27 | Data freeze | (DF) | |
| 28 | 0.02° | | |
| 29 | 0.02 0.08° | | |
| 30 | 0.1° | | BCD outputs |
| 31 | | | _ DCD outputs |
| 32 | 0.4° 2° | | |
| | | | |
| 33 | 8° | | |
| 34 | Not used | | |
| 35 | Not used | | |
| 36 | Spare | | |
| 37 | Spare | _ | |
| 38 | 0.008° | | DCD 4 4 |
| 39 | 0 . 002° | | BCD outputs |
| 40 | 0.001° | | |
| 41 | Spare | | |
| 42 | Data Freeze | (DF) | |
| 43 | Remote Program | | |
| 44 | 0.004° | _ | |
| 45 | 20° | | |
| 46 | 40° | | |
| 47 | 80° | | BCD outputs |
| 48 | 10° | | _ |
| 49 | 100° | | |
| 50 | 200° | | |

ORDERING INFORMATION

To order, specify all parameters using the part numbering system shown below.



^{*}Consult Factory for Operation to 10 KHz

Description of (supplied) Mating Connector Kit (783718)

API parallel I/O 50-pin mating connector, J1 is supplied by North Atlantic Industries, but cable assembly must be made by user. This kit consists of the following parts:

| Description | AMP P/N | Qty |
|-------------|----------|-----|
| Shell | 205211-1 | 1 |
| Clamp | 205732-1 | 1 |
| Retainer | 205980-1 | 2 |
| Pins | 66569-3 | 50 |

Accessories

The API can be ordered with mounting adapters for mounting either one or two units in a standard 19-inch equipment rack. The table below describes full rack and tandem full rack mounting accessories.

| Type of Mount | Description | NAI P/N |
|---------------------------|--|---------|
| Full Rack Mounting | Mounts one unit in 19-inch rack | 783893 |
| Tandem Full Rack Mounting | Mounts two units side by side in 19-inch rack (3-1/2" rack height) | 548557 |

North Atlantic Industries, Inc. 110 Wilbur Place, Bohemia, NY 11716 631.567.1100 / 631.567.1823 (fax) www.naii.com / e-mail:sales@naii.com 2-13-02

Cage Code: OVGU1

8810A001 Rev. C Page 7 of 7